



Approved by







AMX MEDICAL SYSTEMS

AN ISO 9001 : 2008 CERTIFIED CO.

An innovative high image quality with rise to the Next Evolution in X-RAY





Rating - 60mA at 30 to 100 KVP, 40mA at 30 to 100 KVP, 20mA at 30 to 100 KVP.

Micro controller based timer - 0.02 to 10 Sec. in 24 steps. Power Requirement - 8 KVA, 220 Volts, Single Phase, AC supply









Digitone D Dental x-ray machine

10 mA, 70 kVp, 0.01 to 5 seconds micro-processor based timer with R.V.G comparative timer with remote control.

Standard Panoramic
Clear, sharp images with a
wide image layer. The thick,
specifically designed image
layer accommodates all
possible variations of dental
arch shapes and sizes to
produce extremely clear and
sharp images.

Pedodontic Panoramic at
Reduced Radiation
For examinations of children
or people with small jaws, the
rotation range of the arm is
diminished, thereby further
reducing radiation exposure.





